High-Speed & Resolution Analog Input Board for PCI



* Specifications, color and design of the products are subject to change without notice.

This product is PCI-compliant interface boards that convert analog input signals to digital data (performing analog-to-digital conversion). This product carries high-capacity buffer memory for 16M data for analog input, allowing background sampling to be performed in a variety of trigger conditions. This product also has one analog output channel, four channels for TTL level digital input, and four channels for TTL level digital output.

This product is the high-speed, high-precision type that performs A-D conversion at a conversion speed of 1μ sec per channel and a resolution of 16-bit.

Using the bundled API function library package [API-PAC(W32)], you can create Windows application software for this board in your favorite programming language supporting Win32 API functions, such as Visual Basic or Visual C++.

It can also collect data easily without a program when the data logger software [C-LOGGER] stored on the attached Disk is used. With plug-ins for the dedicated libraries, the board also supports MATLAB and LabVIEW.

This product is partly improved from the past analog E series; it is an upward-compatible product. Basically, this product can therefore be used in the same way as the analog E series. This product is different in specification from the E series. The difference point is shown in "Differences between past analog E and this product".

Features

Resolution :16-bit, combination speed : 1µsec/ch

This product is the high-speed, high-precision type that performs A-D conversion at a conversion speed of 1μ sec per channel and a resolution of 16-bit.

The product has analog input 16ch, analog output 1ch, digital input/output (TTL level: four each), and a counter (32-bit, TTL level 1ch). In addition, the analog input can be set to single-end input 16ch or differential input 8ch, while the counter is commonly used as the digital input/output.

Equipped with high-capacity buffer memory for 16M data and a variety of sampling control functions

FIFO or RING buffer memory for 16M data, allowing sampling to be performed as a background task independent of the processing power of the PC.

Capable of starting and stopping sampling not only by software commands but depending on the strength of an analog signal (via conversion data comparison) or by detection of a TTL level signal (external trigger).

Sixteen single-ended channels or eight differential channels (Analog input function)

These boards allow either single-ended or differential input mode that is selected with on-board jumpers. The order of channels subject to signal conversion can be preset in the dedicated register. Using an optional unit, a board can increase the maximum number of input channels (up to 32 channels) and perform simultaneous sampling.

Mixed on-board channels for analog output and digital I/O

One channel for analog output, four channels for TTL level digital input, and four channels for TTL level digital output mixed on the board.

Compact PCI short-size board with a wealth of advanced functions Abundant optional units

Providing a variety of options available for extending the functions, including buffer amplifier, simultaneous sampling, insulation & current/thermocouple input, low pass filter, and cables.

Supported to the data logger software [C-LOGGER]

Supporting the data logger software [C-LOGGER] that enables the graph display of recorded signal data, file saving, and dynamic transfer to the spreadsheet software program "Excel"

Plug-ins for the dedicated libraries, the board also supports MATLAB and LabVIEW.

We offer a dedicated library [ML-DAQ], which allows you to use this product on MATLAB by the MathWorks as well as another dedicated library [VI-DAQ], which allows you to use the product on LabVIEW.

These dedicated libraries are available, free of charge (downloadable), on our web site.

Specification

Specification

Specification		
Item	AD16-16U(PCI)EV	
Analog input		
Isolated specification	Unisolated	
Туре	Single-Ended Input or Differential Input (Jumper setup)	
Number of input	16ch (Single-Ended Input)	
channels	8ch (Differential Input)	
Input range	Bipolar ±10V, ±5V	
	or Unipolar 0 - +10V, 0 - +5V (Jumper setup)	
Absolute max. input	±15V	
voltage		
Input impedance	1MΩ or more	
Resolution	16-bit	
Non-Linearity error *1	±3LSB	
Conversion speed	1μ sec/ch (Max.)	
Buffer memory	16M data FIFO or 16M data RING (Software setup)	
Conversion start trigger	Software/Input data comparison/TTL level external signal	
Conversion stop trigger	Specified sampling data stored /Input data comparison/	
	TTL level external signal/Software	
Analog output		
Isolated specification	Unisolated	
Number of output	1ch	
channel		
Output range	Bipolar ±10V / Unipolar 0 - +10V (Jumper setup)	
Output current ability	±5mA	
Output impedance	1Ω or less	
Resolution	16-bit	
Non- Linearity error *1	±3LSB	
Conversion speed	10μsec/ch (Max.)	
Digital I/O		
Number of input channels	Unisolated input 4ch (TTL level, Selection of a counter output is	
Number of output	possible at a jumper.) Unisolated input 4ch (TTL level, A counter control input and	
channels	common use are possible at a jumper.)	
Counter		
Counter device	i8254 equivalent	
Counter clock	Internal (4MHz) or External signal	
I/O address	Any 32-byte boundary	
Interrupt	1 level use	
Power consumption *4	+5V 1000 mA (Max.)	
Operating condition	0 - 50°C, 10 - 90%RH (No condensation)	
PCI bus specification	32-bit, 33MHz, Universal key shapes supported *5	
Physical dimensions (mm)	176.41(L) x 105.68(H)	
Interface connectors		
CN1	D-SUB 37-Pin female connector #4-40UNC	
CN2	16-pin Pin-header	
Weight	150g	
Certification	RoHS,CE,VCCI	
	temperature is near 0°C or 50°C, the non-linearity error may	

*1 When the environment temperature is near 0°C or 50°C, the non-linearity error may become larger.


*2 At the time of the source use of a signal which built in the high-speed operational amplifier.

*3 An error of about 0.02% of the maximum range value may occur with an unisolated bipolar setting of +5 V or an unisolated unipolar setting of 0 - +5 V.

bipolar setting of ±5 V or an unisolated unipolar setting of 0 - +5 V.
*4 If an external device requires this AD16-16U(PCI)EV board to supply +5VDC from the CN1 or CN2 connectors, the power consumption of this board will be bigger than what this specification has defined.

This board requires +5V power supply from expansion slots (it does not operate in the environment of only +3.3V power supply).

Board Dimensions



the distance from the end of the board to the outer surface of the slot cover.

Support Software

Windows version of analog I/O driver API-AIO(WDM) / API-AIO(98/PC)

[Stored on the bundled Disk driver library API-PAC(W32)]

The API-AIO(WDM) / API-AIO(98/PC) is the Windows version driver library software that provides products in the form of Win32 API functions (DLL). Various sample programs such as Visual Basic and Visual C++, etc and diagnostic program useful for checking operation is provided.

You can download the updated version from the CONTEC's Web site. For more details on the supported OS, applicable language and new information, please visit the CONTEC's Web site.

Linux version of analog I/O driver API-AIO(LNX) [Stored on the bundled Disk driver library API-PAC(W32)]

The API-AIO(LNX) is the Linux version driver software which provides device drivers (modules) by shared library and kernel version. Various sample programs of gcc are provided. You can download the updated version from the CONTEC's Web site. For more details on the supported OS, applicable language and new information, please visit the CONTEC's Web site.

Data Logger Software C-LOGGER [Stored on the bundled Disk driver library API-PAC(W32)]

C-LOGGER is a data logger software program compatible with our analog I/O products. This program enables the graph display of recorded signal data, zoom observation, file saving, and dynamic transfer to the spreadsheet software "Excel". No troublesome programming is required.

CONTEC provides download services to supply the updated drivers. For details, refer to the C-LOGGER Users Guide or our website.

Data acquisition VI library for LabVIEW VI-DAQ (Available for downloading (free of charge) from the CONTEC web site.)

This is a VI library to use in National Instruments LabVIEW. VI-DAQ is created with a function form similar to that of LabVIEW's Data Acquisition VI, allowing you to use various devices without complicated settings. See the CONTEC's Web site for details and download of

VI-DAQ.

Cable & Connector

Cable (Option)

Flat Cable with 37-Pin D-SUB Connector at One End : PCA37P-1.5 (1.5m)

Shield Cable with 37-Pin D-SUB Connector at One End : PCA37PS-0.5P (0.5m)

: PCA37PS-1.5P (1.5m)

Shielded Cable with 37-pin D-SUB connectors at either ends : PCB37PS-0.5P (0.5m)

: PCB37PS-1.5P (1.5m)

Flat Cable with 15-Pin D-SUB Connector at One End : PCA15P-1.5 (1.5m)

Flat Cable with 15-Pin D-SUB Connectors at either Ends : PCB15P-1.5 (1.5m) *1

Coaxial Cable for Single-ended Inputs (16 channels) : PCC16PS-1.5 (1.5m)

: PCC16PS-3 (3m)

2 Wires Shielded Cable for Differential Inputs (8 channels) : PCD8PS-1.5 (1.5m)

: PCD8PS-3 (3m)

Flat Cable with 1 Sided 16-Pin Header Connector (1.5m) : DT/E1

Conversion Cable (16-Pin to 15-Pin) with Bracket (100mm) : DT/E2

Conversion Cable (16-Pin to 15-Pin) with Bracket (150mm) : DT-E3

Connector (Option)

37-pin D-SUB (Male) Connector Set (5 Pieces) : CN5-D37M

```
*1 For FTP-15 only
```

Accessories

Accessories (Option)

BNC Terminal Unit (for analog input 16ch)	: ATP-16E *1
Buffer Amplifier Box for Analog Input Boards (16ch type)	: ATBA-16E *1
General Purpose Terminal (M3 x 15P)	: FTP-15 *2
Screw Terminal Unit (M3 x 37P)	: EPD-37A *1 *3
Screw Terminal Unit (M3.5 x 37P)	: EPD-37 *1
General Purpose Terminal (M3 x 37P)	: DTP-3A *1
Screw Terminal (M2.6 x 37P)	: DTP-4A *1
16 Channel Simultaneous Sample & Hold Board	: ATSS-16 *1
8ch- Isolated Expansion Accessory Board for Analog Input	: ATII-8C *1
8ch- Isolated Expansion Accessory Board for Analog Input	: ATII-8A *1
Low Pass Filter Accessory for Analog Input	: ATLF-8A*1
16CH Multiplexer Sub-Board for AD12-16U(and AD16-16U(PCI)EV	PCI)EV : ATUH-16A(PCI)
*1 A PCR37PS -*P ontional cable is required separately (0.5m	is recommended)

*1 A PCB37PS -*P optional cable is required separately. (0.5m is recommended.)


*2 A DT/E2 and PCB15P-1.5 optional cable is required separately.
*3 "Spring-up" type terminal is used to prevent terminal screws from falling off.

* Check the CONTEC's Web site for more information on these options.

Packing List

Board [AD16-16U(PCI)EV] ...1 First step guide ... 1 Disk *1 [API-PAC(W32)]...1 Serial number label...1 Product Registration Card & Warranty Certificate...1

*1 The CD-ROM contains the driver software and User's Guide.




How to connect the connectors


Connector shape

To connect an external device to this board, plug the cable from the device into the interface connector (CN1, CN2) shown below.

The board has two interface connectors: the analog I/O connector (CN1: 37-pin female D-SUB connector) and the control signal connector (CN2: 16-pin pin-header) for digital input/output and counter control.



Please refer to this page for more information on the supported cable and accessories.



Connector Pin Assignment Pin Assignment of CN1

< Single-Endedn Input >	< Differential Input >
CN1 Digital Ground 47 19 ++5V DC from PC Analog Ground 47 18 ++5W DC from PC Analog Ground 47 18 ++5W DC from PC Analog Ground 47 18 + Chanlog Input 15 Analog Ground 47 11 16 + Analog Input 17 Analog Ground 47 11 16 + Analog Input 18 Analog Ground 47 11 17 + Analog Input 18 Analog Ground 47 11 17 + Analog Input 18 Analog Ground 47 19 10 + Analog Input 18 Analog Ground 47 19 10 + Analog Input 18 Analog Ground 47 18 + Analog Input 10 Analog Ground 47 18 + Analog Input 10 Analog Ground 47 18 + Analog Input 10 Analog Ground 47 18 + Analog Input 19 Analog Ground 47 18 + Analog Input 19 Analog Ground 47 18 + Analog Input 19 Analog Ground 47 18 + Analog Input 1 Analog Ground 47 + Analog Input 1 Analog From 47 + Analog Input 1 Analog Ground 47 + Analog Input 1 Analog Analog Fround 47 + Analog Input 1 Analog Fround 47 + Analog Inpu	$\begin{array}{c} \text{CN1} \\ \hline \\ \text{Digital Ground} & -37 & 19 & +5V \text{ DC from PC} \\ \text{Analog Ground} & -36 & 17 & -\text{Manlog Output} \\ \text{Analog Ground} & -35 & 16 & -\text{Analog Input 7} & [-1] \\ \text{Analog Ground} & -33 & 15 & -\text{Analog Input 7} & [+1] \\ \text{Analog Ground} & -33 & 15 & -\text{Analog Input 6} & [+] \\ \text{Analog Ground} & -33 & 13 & -\text{Analog Input 6} & [+] \\ \text{Analog Ground} & -33 & 11 & -\text{Analog Input 6} & [+] \\ \text{Analog Ground} & -33 & 11 & -\text{Analog Input 6} & [+] \\ \text{Analog Ground} & -30 & 11 & -\text{Analog Input 6} & [+] \\ \text{Analog Ground} & -30 & 11 & -\text{Analog Input 6} & [+] \\ \text{Analog Ground} & -39 & 10 & -\text{Analog Input 6} & [+] \\ \text{Analog Ground} & -28 & 19 & -\text{Analog Input 4} & [+] \\ \text{Analog Ground} & -25 & 6 & -\text{Analog Input 3} & [-] \\ \text{Analog Ground} & -25 & 6 & -\text{Analog Input 2} & [+] \\ \text{Analog Ground} & -23 & 2 & -\text{Analog Input 1} & [+] \\ \text{Analog Ground} & -23 & 4 & -\text{Analog Input 1} & [+] \\ \text{Analog Ground} & -21 & 2 & -\text{Analog Input 1} & [+] \\ \text{Analog Ground} & -21 & 2 & -\text{Analog Input 1} & [+] \\ \text{Analog Ground} & -21 & 2 & -\text{Analog Input 1} & [+] \\ \text{Analog Ground} & -21 & 2 & -\text{Analog Input 1} & [+] \\ \text{Analog Ground} & -21 & 2 & -\text{Analog Input 1} & [+] \\ \text{Analog Ground} & -21 & 2 & -\text{Analog Input 1} & [+] \\ \text{Analog Ground} & -21 & 2 & -\text{Analog Input 1} & [+] \\ \text{Analog Ground} & -21 & 2 & -\text{Analog Input 1} & [+] \\ \text{Analog Ground} & -21 & 2 & -\text{Analog Input 1} & [+] \\ \text{Analog Ground} & -21 & 2 & -\text{Analog Input 1} & [+] \\ \text{Analog Ground} & -21 & 2 & -\text{Analog Input 1} & [+] \\ \text{Analog Ground} & -21 & 2 & -\text{Analog Input 1} & [+] \\ \text{Analog Ground} & -21 & 2 & -\text{Analog Input 1} & [+] \\ \text{Analog Ground} & -21 & 2 & -\text{Analog Input 1} & [+] \\ \end{array} \end{bmatrix}$

Analog Input 0	Analog input signals in single-ended input mode.	
- Analog Input 15	The numbers correspond to channel numbers.	
Analog Input 0[+]	Analog input signals in differential input mode.	
- Analog Input 7[+]	The numbers correspond to channel numbers.	
Analog Input 0[-]	Analog input signals in differential input mode.	
- Analog Input 7[-]	The numbers correspond to channel numbers.	
Analog Output	Analog output signal	
Analog Ground	Analog ground common to analog I/O signals.	
Simultaneous Hold	Control signal for simultaneous sampling unit ATSS-16 available as	
Output	an option.	
+5V DC from PC	Supplies 2A of current at +5 V.	
Digital Ground	Digital ground common to "Simultaneous Hold Output" and "+5V DC from PC".	

▲ CAUTION

Do not connect any of the outputs and power outputs to the analog or digital ground.

Neither connect outputs to each other. Doing either can result in a fault.

Pin Assignment of CN2

	CN9
External Sampling	
/ Digital Input 2 Dig	rigger Input B5 A5 Digital Input 3 / INT Trigger CNT Clock B4 A4 Digital Input 1 / CNT Gate rital Input 0 B3 A3 Digital Ground
Digital Output 3 / C Digit	NT Output B2 A2 Digital Output 2 al Output 1 B1 A1 Digital Output 0
Digital Input 0	Digital input signal.
Digital Input 1 /CNT Gate	Digital input signal. Also serving as the counter gate control input signal.
Digital Input 2 /CNT Clock	Digital input signal. Also serving as the clock input signal
Digital Input 3 /INT Trigger	Digital input signal. Also serving as the interrupt input signal.
Digital Out 0 to Digital Out 2	Digital output signal.

Digital Out 3	Digital output signal.	
to CNT Output	Capable of being jumper-switched to serve as the counter output	
-	signal.	
External Start Trigger Input	External trigger input signal for sampling start conditions	
External Stop Trigger Input	External trigger input signal for sampling stop conditions	
External Sampling Clock	External sampling clock input signal	
Input		
Sampling Clock Output	Sampling clock output signal	
+5V DC from PC	Supplies 1A of current at +5 V.	
Digital Ground	Digital ground common to the signals and "+5V DC from PC".	
N.C.	No connection to this pin.	

A CAUTION

Do not connect any of the outputs and power outputs to the analog or digital ground.

Neither connect outputs to each other. Doing either can result in a fault.

Analog Input Signal Connection

There are two analog input modes: the Single-ended input and the Differential input. Here we give some examples of analog input connections by using flat cable or shield cable.

Single-ended Input


The following figure shows an example of flat cable connection. Each signal source is connected to one analog input channel and the signal common to analog ground pin of CN1.

Single-ended Input Connection (Flat Cable)

BOARD	CN1	Cable	,	Signal Source
Analog Input 015	ċ			
Analog Ground	•			
	. ↓ ↓		:	$\frac{1}{2}$

The following figure shows an example of shield cable connection. When the distance between the signal source and the board is long or you want to increase the noise tolerance, a shield cable is suggested. Connect the signal by the core wire and common signal by the shield braids.

Single-ended Input Connection (Shield Cable)



A CAUTION

If the signal source contains over 1MHz signals, the signal may effect the cross-talk noise between channels.

If the board and the signal source receive noise or the distance between the board and the signal source is too long, data may not be input properly.

An input analog signal should not exceed the maximum input voltage (relate to the board analog ground). If it exceeds the maximum voltage, the board may be damaged.

Connect all the unused analog input channels to analog ground.

Differential Input


The following figure shows an example of flat cable connection. Each signal source is connected to a [+] pin of analog input channel and the signal common of this source to the [-] pin of this input channel of CN1. In addition, the signal common must be connected to the pin of the analog ground of CN1 by a third wire.

Differential Input Connection (Flat Cable)

BOARD	CN1	Cable	Signal Source
Analog Input 0[+]7[+]	ò		¢
Analog Input 0[-]7[-]	o		→ <u> </u>
Analog Ground	,		
•	÷ ÷		·

The following figure shows an example of 2-wire shielded cable connection. When the distance between the signal source and the board is long or you want to increase the noise tolerance, a shield cable connection is preferred. Each signal source is connected to a [+] pin of analog input channel and the signal common of this source to the [-] pin of this input channel of CN1. In addition, the signal common must be connected to the pin of the analog ground of CN1 by the shielded braids.

Differential Input Connection (Shield Cable)



A CAUTION

If the signal source contains over 1MHz signals, the signal may effect the cross-talk noise between channels.

The input data would be uncertain if the analog ground is not connected.

If the board and the signal source receive noise or the distance between the board and the signal source is too long, data may not be input properly.

The input voltage from the [+] input or [-] input should not exceed the maximum input voltage (based on the board analog ground). If it exceeds the maximum voltage, the board may be damaged.

Because the input data will be uncertain if the [+] pin or the [-] pin of CN1 is not connected, all the unused input pins of CN1 should be connected to the analog ground, AGND.

Analog Output Signal Connection

This section shows how to connect the analog output signal by using a flat cable or a shielded cable.


The following figure shows an example of flat cable connection. Connect the signal source and ground to the CN1 analog output.

Analog Output Connection (Flat Cable)

BOARD	CN1	Cable	, 	Target
Analog Output	o			$(\underline{V})^{\dagger}$
Analog Ground	Ψ ^γ			<u>_</u>

If the distance between the signal source and the board is long or if you want to increase the noise tolerance, a shield cable connection is strongly recommended.

Analog Output Connection (Shield Cable)



A CAUTION

If the board or the connected wire receives noise, or the distance between the board and the target is long, data may not be outputted properly.

For analog output signal, the current capacity is ±5mA (Max.). Check the specification of the connected device before connecting the board.


Do not short the analog output signal to analog ground, digital ground, and/or power line. Doing so may damage the board.

Digital I/O signals and Control signals Connection


The digital I/O signals and the control signals are interfaced through the connector CN2. User can use an optional cable DT/E1 or DT/E2 or DT-E3 (with bracket and a 15-pin D type female connector) to connect these signals to your external devices.

All the digital I/O signals and control signals are TTL level signals.

Digital Input Connection



Digital Output Connection



A CAUTION

Do not short the output signals to analog ground, digital ground, and/or power line. Doing so may damage the board.

Differences between past analog E and this product

This product is a product that partially improves a past analog E series, and the upper compatibility goods of the analog E series. Therefore, the same usage as the E series can be basically done.

There are some differences in specifications as shown below.

Past E Series	: AD16-16U(PCI)EH
This product	: AD16-16U(PCI)EV

	AD16-16U(PCI)EH	AD16-16U(PCI)EV
Power consumption	+5V 1400mA (Max.)	+5V 1000 mA (Max.)
Physical Dimension (mm)	176.41(L) x 106.68(H)	176.41(L) x 105.68(H)