© CONTEC Ver.1.05

Isolated 16-bit Analog Output Board for PCI Express

AO-1604LI-PE



* Specifications, color and design of the products are subject to change without notice.

Features

Bus isolated high precision analog output 4 channels, each 4 channels for digital I/O, counter 1 channel

This product has analog output (10µsec [100KSPS], 16-bit, 4 channels), analog output control signal (Isolation TTL level 3 channels), digital I/O (4 channels each for Isolation TTL level), counter (32-bit, Isolation TTL level 1 channel).

Functions and connectors are compatible with PCI compatible board DAI16-4(LPCI)L

The functions same with PCI compatible board DAI16-4(LPCI)L are provided. In addition, as there is compatibility in terms of connector shape and pin assignments, it is easy to migrate from the existing system.

Bus isolation between PC and external I/O signals by a digital isolator Isolation between PC and external I/O circuit by a digital isolator improves noise tolerance.

The start/end of sampling can be controlled by software, an external trigger, etc.

You can select from software, an external trigger to control the start of sampling. You can select from completion of sampling for a specified number of sessions, an external trigger or software to control forcibly the end of sampling. The sampling cycle can be selected from the internal clock or an external clock.

Safety design to adjust output voltage to 0V when power supply is turned on

To prevent the unstable voltage and the connected device of D/A converter from fault and malfunctions when the power supply is turned on, the circuit is designed to adjust output voltage of the analog output to OV.

Equipped with buffer memory (1K data) that can be used in the FIFO or RING format

The analog output block contains buffer memory (1K data) that can be used in the FIFO or RING format. This allows for background analog output that does not depend on the operation status of the software or

Digital filter function included to prevent misdetection due to chattering on external signals

A digital filter is included to prevent misdetection due to chattering on the control signal (external trigger input signal, sampling clock input signal, etc.), digital input signal and counter input signal.

(Except from external clock input signal and counter gate signal)

This product is a PCI Express bus-compliant interface board used to provide an analog signal output, output function on a PC.

AO-1604LI-PE features bus isolated 16-bit analog output 4 channels. Equipped with digital I/O and counter, this product is multifunction and bus isolated type that provides isolation between PC and external analog I/O circuit. This product carries buffer memory for 1K of data, allowing sampling to be performed in a variety of trigger / clock conditions

Windows/Linux driver and full-fledged data logger software "C-LOGGER" is bundled with this product. Possible to be used as a data recording device for MATLAB and LabVIEW, with dedicated libraries.

- * The contents in this document are subject to change without notice.
- * Visit the CONTEC website to check the latest details in the document.
- * The information in the data sheets is as of January, 2018.

Software-based calibration function

Calibration can be all performed by software. Apart from the adjustment information prepared before shipment, additional adjustment information can be stored according to the use environment.

Data logger software, Windows/Linux compatible driver libraries are attached.

Using the bundled data logger software "C-LOGGER" allows you to display recorded signal data in graphs, save files without any special program. In addition, the driver library API-PAC(W32) which makes it possible to create applications of Windows/Linux is provided.

MATLAB and LabVIEW is supported by a plug-in of dedicated library VI-DAQ.

Using the dedicated library MATLAB and VI-DAQ makes it possible to make a LabVIEW application.

Packing List

Board [AO-1604LI-PE] ...1

First step guide ... 1

Disk *1 [API-PAC(W32)] ...1

Warranty Certificate ...1

Serial Number Label ...1

*1 The bundled disk contains the driver software and User's Guide.

List of Options

Shield Cable with 50-Pin Mini-Ribbon Connectors

at either Ends :PCB50PS-0.5P (0.5m)

:PCB50PS-1.5P (1.5m)

Shield Cable with 50-Pin Mini-Ribbon Connector

at one End :PCA50PS-0.5P (0.5m)

:PCA50PS-1.5P (1.5m)

:EPD-50A *1*2

:ATBA-8L *1*3

Screw Terminal Unit (M3 x 50P)

Buffer Amplifier Box for Analog Input Boards

(8ch type)

Buffer Amplifier Box for Analog Input Boards

(16ch type) :ATBA-16L *1*3

BNC Terminal Unit

(for analog input 8ch) :ATP-8L *1*4

- *1 PCB50PS-0.5P or PCB50PS-1.5P optional cable is required separately.
- *2 "Spring-up" type terminal is used to prevent terminal screws from falling off.
- *3 An external power supply is necessary (optional AC adaptor POA200-20 prepared.)
- *4 Capable of using the analog input of up to 8ch, and analog output of up to 2ch.


 * Check the CONTEC's Web site for more information on these options.

Specification

Item	Specifications					
Analog output						
Isolated specification	Bus-Isolated					
Number of output channels	4ch					
Output range	Bipolar ±10V					
Absolute max. output currency	±5mA					
Output impedance	1Ω or less					
Resolution	16bit					
Non-Linearity error *1	±5LSB					
Conversion speed	10μsec [100KSPS]*2					
Buffer memory	1k Word					
Conversion start trigger	Software / external trigger					
Conversion stop trigger	Number of sampling times / external trigger/software					
External start signal	Isolation TTL-level (Rising or falling edge can be selected by software) Digital filter (1µsec can be selected by software)					
External stop signal	Isolation TTL-level (Rising or falling edge can be selected by					
External stop signal	software) Digital filter (1µsec can be selected by software)					
External clock signal	Isolation TTL-level (Rising or falling edge can be selected by software)					
Digital I/O						
Number of input channels	Isolated input 4ch (TTL-level positive logic)					
Number of output channels	Isolated input 4ch (TTL-level positive logic)					
Counter						
Number of channels	1ch					
Counting system	Up count					
Max. count	FFFFFFFh (Binary data,32bit)					
Number of external	2 Isolation TTL-level (Gate/Up)					
inputs	Gate (positive logic/level), Up (Rising edge)					
Number of external	1 Isolation TTL-level					
outputs	Count match output (positive logic, pulse output)					
Response frequency	1MHz (Max.)					
Common section						
I/O address	64 ports					
Interruption level	Errors and various factors, One interrupt request line as INTA					
Connector	10250-52A2JL[3M]					
Power consumption	3.3VDC 1500 mA (Max.)					
Operating condition	0 - 50°C, 10 - 90%RH (No condensation)					
Bus specification	PCI Express Base Specification Rev. 1.0a x1					
Dimension (mm)	169.33 (L) x 110.18(H)					
Weight	120 g					

- *1 The non-linearity error means an error of approximately 0.1% occurs over the maximum range at 0°C and 50°C ambient temperature.
- *2 SPS = Samplings Per Second. The number of data that can be converted in one second is shown

Dimensions



Support Software

Windows version of analog I/O driver API-AIO(WDM)

[Stored on the bundled disk driver library API-PAC(W32)]

The API-AIO(WDM) is the Windows version driver library software that provides products in the form of Win32 API functions (DLL). Various sample programs such as Visual Basic and Visual C++, etc and diagnostic program *1useful for checking operation is provided.

For more details on the supported OS, applicable language and new information, please visit the CONTEC's Web site.

Linux version of analog I/O driver API-AIO(LNX)

[Stored on the bundled disk driver library API-PAC(W32)]

The API-AIO(LNX) is the Linux version driver software which provides device drivers (modules) by shared library and kernel version. Various sample programs of gcc are provided.

For more details on the supported OS, applicable language and new information, please visit the CONTEC's Web site.

Data Logger Software C-LOGGER

[Stored on the bundled disk driver library API-PAC(W32)] C-LOGGER is a data logger software program compatible with our analog I/O products. This program enables the graph display of

recorded signal data, zoom observation, file saving, and dynamic transfer to the spreadsheet software "Excel". No troublesome programming is required.

For more details on the supported OS, applicable language and new information, please visit the CONTEC's Web site.

Data Acquisition library for MATLAB ML-DAQ

(Available for downloading (free of charge) from the CONTEC web site.)

This is the library software which allows you to use our analog I/O device products on MATLAB by the MathWorks. Each function is offered in accordance with the interface which is integrated in MATLAB's Data Acquisition Toolbox.

For more details on the supported OS, applicable language and new information, please visit the CONTEC's Web site.

Data acquisition VI library for LabVIEW VI-DAQ

(Available for downloading (free of charge) from the CONTEC web site.)


This is a VI library to use in National Instruments LabVIEW. VI-DAQ is created with a function form similar to that of LabVIEW's Data Acquisition VI, allowing you to use various devices without complicated settings.

For more details on the library and download of VI-DAQ, please visit the CONTEC's Web site.

How to connect the connectors

Connector shape

To connect an external device to this board, plug the cable from the device into the interface connector (CN1) shown below.



50-pin mini-ribbon connector 10250-52A2JL[mfd.by 3M]

- Compatible connector 10150-6000EL[mfd. by 3M]

Connector Pin Assignment

Pin Assignments of AO-1604LI-PE Interface Connector (CN1)

Analog Output 02	AO 02	50						25	AO 00	Analog Output 00
Analog Ground (for AO)	AGND	49						24	AGND	Analog Ground (for AO)
Analog Output 03	AO 03	48						23	AO 01	Analog Output 01
Analog Ground (for AO)	AGND	47						22	AGND	Analog Ground (for AO)
Non Connect	N.C.	46		_	_			21	N.C.	Non Connect
Non Connect	N.C.	45	50 -	\vdash	_	_	25	20	N.C.	Non Connect
Non Connect	N.C.	44						19	N.C.	Non Connect
Non Connect	N.C.	43						18	N.C.	Non Connect
Reserved	Reserved	42						17	Reserved	Reserved
Reserved	Reserved	41						16	Reserved	Reserved
Non Connect	N.C.	40						15	N.C.	Non Connect
Non Connect	N.C.	39						14	N.C.	Non Connect
Non Connect	N.C.	38						13	N.C.	Non Connect
Non Connect	N.C.	37						12	N.C.	Non Connect
AO External Start Trigger Input	AO START	36						11	N.C.	Non Connect
AO External Stop Trigger Input	AO STOP	35						10	N.C.	Non Connect
AO External Sampling Clock	AO EXCLK	34						9	N.C.	Non Connect
Digital Ground	DGND	33						8	DGND	Digital Ground
Digital Output 00	DO 00	32						7	DI 00	Digital Input 00
Digital Output 01	DO 01	31	26-	t	,	/	- 1	6	DI 01	Digital Input 01
Digital Output 02	DO 02	30			_			5	DI 02	Digital Input 02
Digital Output 03	DO 03	29						4	DI 03	Digital Input 03
Digital Ground	DGND	28						3	DGND	Digital Ground
Counter UP Clock Input	CNT UPCLK	27						2	CNT GATE	Counter Gate Control
Reserved	Reserved	26						1	CNTOUT	Counter Output

	Analog Output00 - Analog	Analog output signal. The numbers correspond to channel							
	Output03	numbers.							
Analog Ground		Common analog ground for analog I/O signals.							

AO External Start Trigger Input	External trigger input for starting analog output sampling.
AO External Stop Trigger Input	External trigger input for stopping analog output sampling.
AO External Sampling Clock Input	External sampling clock input for analog output.
Digital Input00 - Digital Input03	Digital input signal.
Digital Output00 - Digital Output03	Digital output signal.
Counter Gate Control Input	Gate control input signal for counter.
Counter Up Clock Input	Count-up clock input signal for counter.
Counter Output	Counter output signal.
Digital Ground	Common digital ground for digital I/O signals, external trigger inputs, external sampling clock inputs, and counter I/O signals.
Reserved	Reserved pin.
N.C.	No connection to this pin.

CAUTION

- Do not connect any of the outputs and power outputs to the analog or digital ground.
 Neither connect outputs to each other. Doing either can result in a fault.
- If analog and digital ground are shorted together, noise on the digital signals may affect the analog signals. Accordingly, analog and digital ground should be separated.
- Leave "Reserved" pins unconnected. Connecting these pins may cause a fault in the board.

Analog Output Signal Connection

This section shows how to connect the analog output signal by using a flat cable or a shielded cable.


The following figure shows an example of flat cable connection. Connect the signal source and ground to the CN1 analog output.

Analog Output Connection (Flat Cable)



The following figure shows an example of shield cable connection. Use shielded cable if the distance between the signal source and board is long or if you want to provide better protection from noise. For each analog input channel on CN1, connect the core wire to the signal line and connect the shielding to ground.

Analog Output Connection (Shield Cable)



*2 The number of channels depends on each board. The AO-1604LI-PE has four channels

CAUTION


- When the power supply is turned on, the output voltage of all channels becomes OV.
- If the board or the connected wire receives noise, or the distance between the board and the target is long, data may not be outputted properly.
- Do not short the analog output signal to analog ground, digital ground, and/or power line.
 Doing so may damage the board.
- Do not connect an analog output signal to any other analog output, either on the board or on an external device, as this may cause a fault on the board.
- Analog ground of CN1 is isolated from the ground in the PC.

Digital I/O signals, Counter signals and Control signals Connection


The following sections show examples of how to connect digital I/O signals, counter I/O signals, and other control I/O signals (external trigger input signals, sampling clock input signals, etc.).

All the digital I/O signals and control signals are TTL level signals.

Digital Input Connection



Digital Output Connection




About the counter input control signal

Counter Gate Control Input (refer to the chapter 3 Connector Pin Assignment) acts as an input that validate or invalidate the input of an external clock for the counter. This function enables the control of an external clock input for the counter. The external clock for the counter is effective when input is "High", and invalid when input is "Low". If unconnected, it is a pull-up in the board (card) and remains "High". Therefore the external clock for the counter is effective when the counter gate control input is not connected.

CAUTION

- Do not short the output signals to analog ground, digital ground, and/or power line. Doing so may damage the board.
- Do not connect a digital output signal to any other digital output, either on the board or on an
 external device, as this may cause a fault on the board.
- Analog ground of CN1 is isolated from the ground in the PC.

Block Diagram





Difference from DAI16-4(LPCI)L

The functions same with conventional product of DAI16-4(LPCI)L are provided with the AO-1604LI-PE. In addition, as there is compatibility in terms of connector shape and pin assignments, it is easy to migrate from the existing system. So you can use the same operating procedures as DAI16-4(LPCI)L.

There are some differences in specifications as shown below.

	AO-1604LI-PE	DAI16-4(LPCI)L				
Power consumption	+3.3VDC 1500 mA (Max.)	+5VDC 800mA (Max.)				
Bus specification PCI Express Base Specification Rev. 1.0a x1		PCI (32-bit, 33MHz, Universal key shapes supported)				
Dimension (mm)	169.33(L) x 110.18(H)	121.69(L) x 63.41(H)				
Weight	120g	65g				